

PRODUCT CODE:
PENUSG

THORZT
HYDRATING HARD WORK

REFRACTOMETER USG PEN

FEATURES & BENEFITS

- Convenient and easy to use in assessing hydration status
- Digital refractometer for a more accurate Urine Specific Gravity (USG) reading
- Delivers a nearly instantaneous result of USG
- Automatically calibrates itself to water and is ready to use in seconds
- LCD display is easily read, even with dim light

APPLICATIONS

- Indoor / outdoor work
- Sporting events
- Family use

USING A REFRACTOMETER

While urine colour works well as a quick and easy guide, a far more accurate reading can be attained by using a Refractometer. The ATAGO Pen Refractometer (Model No. 3471) is designed to measure USG (Urine Specific Gravity), being a more effective and efficient way to assess hydration status.

Lighter coloured urine is more dilute (i.e. it has less molecules per volume), and has a specific gravity closer to that of water (1.00), indicating a good hydration status. Dark coloured urine results from having more molecules per volume (higher USG) and indicates dehydration.



PENUSG



SCAN TO
WATCH VIDEO

THORZT AUSTRALIA
12 FELLOWSHIP ROAD
GNANGARA, WA 6077
TECH SUPPORT: 1800 846 798
CUSTOMER SERVICE: 1800 846 798
EMAIL: INFO@THORZT.COM

THORZT NEW ZEALAND
7 SIR WOLFF FISHER DRIVE, Highbrook,
EAST TAMAKI, AUCKLAND 2013
TECH SUPPORT: 0800 846 798
CUSTOMER SERVICE: 0800 846 798
EMAIL: ORDERS@PARAMOUNTSAFETY.CO.NZ

THORZT.COM
PARAMOUNTSAFETYPRODUCTS.COM

THORZT
HYDRATING HARD WORK
FROM
PARAMOUNT
SAFETY PRODUCTS